

VBM TL

The **VBM TL** features tilting and lifting functionalities through a symmetrical and aesthetic set of magnet handles located on the right and left edges of the sealed units. It allows simple and smooth operation of the blinds by a swipe of the magnetic handle.


The **VBM TL** is available with 20 and 25 air cavity.




DETAILED DIMENSIONS in mm

VBM TL 20mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D




MAGNET GUIDE




DETAILED DIMENSIONS in mm

VBM TL 25mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D



MAGNET GUIDE



FEASIBILITY

To select the unit configuration compatible with the opening dimensions, consult the table below.

NOTE

Height must be > 50% of the width.


Height (cm)	Width (cm)													
	50	60	70	80	90	100	110	120	130	140	150	160	170	180
60														
70														
80														
90														
100														
110														
120														
130														
140														
150														
160														
170														
180														
190														
200														
210														
220														

Inner pane must be 4mm thick or thinner

VBM TOH


The tilt magnetic handle is positioned on the top or bottom of the double glazed unit and is operated horizontally.

The **VBM TOH** is available with 18, 20 and 25 air cavities.




DETAILED DIMENSIONS in mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D




MAGNET GUIDE




DETAILED DIMENSIONS in mm

VBM TOH 20mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D




MAGNET GUIDE




DETAILED DIMENSIONS in mm

VBM TOH 25mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D



MAGNET GUIDE



VBM TOV

The tilt magnetic handle is positioned on the left or right of the Double glazed unit and is operated horizontally.


The **VBM TOV** is available with 18, 20 and 25 air cavities




DETAILED DIMENSIONS in mm

VBM TOV 18mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D




MAGNET GUIDE




DETAILED DIMENSIONS in mm

VBM TOV 20mm


SECTION A-A




SECTION B-B




SECTION C-C



SECTION D-D




MAGNET GUIDE




DETAILED DIMENSIONS in mm

VBM TOV 25mm


SECTION A-A




SECTION B-B



SECTION C-C



SECTION D-D



MAGNET GUIDE

